


SIM LAB

INSTRUCTION MANUAL



SWIVEL MOUNTING POINT

VERSION 1.01

Last updated: 18-12-2024

BEFORE YOU START:

Thank you for purchasing this Sim-Lab product! On the following pages, you will find detailed instructions on assembly. This requires only a set of simple tools and some of your time. Please check the bill of materials before starting (page 9) and make sure all the parts are delivered.


When adding side mounts, ease of entry is a recurring topic which customers bring up. We wanted to be able to open and close the side mount, to get in and out of your cockpit more easily. Our magnetic catch keeps our swivel mounting point closed during use and solves this problem once and for all!

Please take heed of the warnings on the packaging/parts if these apply to you. Do not hesitate and ask for help or supervision during assembly, we value your health.


This product only consists of the what the name implies. To be able to mount joysticks or throttles, you will need to make an additional purchase of the appropriate accessory such as the 'Joystick Mount' or 'Throttle Mount'.

Inserting Slot-Nuts:


You got excited, finished the build, put the caps on, but forgot to install one element. Do not worry. It happens to everyone. In this diagram, you can see how to insert a Slot-Nut directly into the slot from the side. You can also use one of your smaller Hex wrenches to help wiggle the Slot-Nut in place.



Tools needed:




4/5/6MM




400MM

Profile 80X40
End-Cap


Slot-Nut M8




1X












2X










2X




450MM	Profile 80X40 End-Cap	Corner Bracket	Joint 40	M8 X 16	Washer M8	Slot-Nut M8	Slot-Nut M6 (A15)
							
1X	1X	2X	2X	4X	2X	4X	2X






Magnet Base	M6 X 16	Slot-Nut M8	Slot-Nut M6 (A15)
			
1X	2X	2X	2X



M8 X 16




2X




M8 X 16



Washer M8







2X



2X





The magnet catch prevents the mounting point/side mount to swivel open during use.

Adjust the countersunk bolts on the joints top adjust their tension.

CENTER POST PROFILE KIT			
#	Part	QTY	Note
A1	80X40 Length=450mm	1	
A2	80X40 Length=400mm	1	
HARDWARE KIT			
A3	Magnet base	1	
A4	Magnet catch	1	
A5	Corner bracket	2	
A6	Corner bracket cap	2	
A7	Joint 40	2	
A8	Profile 80x40 end-cap	3	
A9	Bolt M8 X 16 DIN 912	8	
A10	Bolt M6 X 16 DIN 912	2	
A11	Bolt M6 X 16 DIN 7991	2	
A12	Washer M8 DIN 125-A	4	
A13	Washer M6 DIN 125-A	2	
A14	Slot-Nut M8	8	
A15	Slot-Nut M6	4	

If you still have some questions regarding assembly of this product or about the manual itself, please refer to our support department. They can be reached at

support@sim-lab.eu

Alternatively, we now have a Discord server where there are quite some experienced Sim-Lab customers hanging out. They might just help you along if you ask them nicely ;)

www.sim-lab.eu/discord

If you feel like printing this manual, please consider the environment before doing so. For the best results, make sure you print at 100% scale without borders.